



# Intelligent Sereno TBS869/528

## TBS869 C 3xTL5-14W HFR D8 FTB

3, TL5, 14 W, HF Regulator, Semi-high-gloss optic 3D micro-lamellae, Fused terminal block

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFR [HF Regulator]
Embedded control	-
Light Technical	
Number of light sources	3
Optic type	Semi-high-gloss optic 3D micro-lamellae
Operating and Electrical	
Power Consumption	14 W
Cable	-

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	TBS869 C 3xTL5-14W HFR D8 FTB
Full product name	TBS869 C 3xTL5-14W HFR D8 FTB
Full product code	910403630613
Order code	910403630613
Material Nr. (12NC)	910403630613
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Intelligent Sereno TBS869/528

### Dimensional drawing

