



Intelligent Sereno TBS869/528

TBS528 2xTL5-28W HFR M8 FTB

2, TL5, 28 W, HF Regulator, Matt optic 3D micro-lamellae, Fused terminal block

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFR [HF Regulator]
Embedded control	-
Light Technical	
Number of light sources	2
Optic type	Matt optic 3D micro-lamellae
Operating and Electrical	
Power Consumption	28 W
Cable	-
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Product Data	
Order product name	TBS528 2xTL5-28W HFR M8 FTB
Full product name	TBS528 2xTL5-28W HFR M8 FTB
Full product code	910403630615
Order code	910403630615
Material Nr. (12NC)	910403630615
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291994466
Numerator - Packs per outer box	2
EAN/UPC - Case	8718291994466

Intelligent Sereno TBS869/528

Dimensional drawing

