



# Intelligent Sereno TBS869/528

## TBS869 C 1xTL5-28W HFP WV D8-H FTB

1, TL5, 28 W, Electronic Primalume, Semi-high-gloss optic 3D micro-lamellae high reflectance, Fused terminal block

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EBP [Electronic Primalume]
Embedded control	-
Light Technical	
Number of light sources	1
Light source color	-
Optic type	Semi-high-gloss optic 3D micro-lamellae high reflectance
Operating and Electrical	
Power Consumption	28 W
Cable	-

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	TBS869 C 1xTL5-28W HFP WV D8-H FTB
Full product name	TBS869 C 1xTL5-28W HFP WV D8-H FTB
Full product code	910403630641
Order code	910403630641
Material Nr. (12NC)	910403630641
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Intelligent Sereno TBS869/528

### Dimensional drawing

