



Intelligent Sereno TBS869/528

TBS528 1x35W HFP O FU TLR-T24 WH

1, 35 W, HF Performer, Opal, Fuse included, White

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	White
Gear	HFP [HF Performer]	Approval and Application	
Embedded control	-	Ingress protection code	IP20 [Finger-protected]
Light Technical		Product Data	
Number of light sources	1	Order product name	TBS528 1x35W HFP O FU TLR-T24 WH
Light source color	-	Full product name	TBS528 1x35W HFP O FU TLR-T24 WH
Optic type	-	Order code	910403630663
Optical cover type	Opal	Material Nr. (12NC)	910403630663
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	35 W	Numerator - Packs per outer box	2
Cable	-		

Intelligent Sereno TBS869/528

Dimensional drawing

