



# Intelligent Sereno TBS869/528

## TBS528 1x49W HFP O FU TLR-T24 WH

1, 49 W, HF Performer, Opal, Fuse included, White

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

### Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	White
Gear	HFP [HF Performer]		
Embedded control	-		
Light Technical		Approval and Application	
Number of light sources	1	Ingress protection code	IP20 [Finger-protected]
Light source color	-		
Optic type	-	Product Data	
Optical cover type	Opal	Order product name	TBS528 1x49W HFP O FU TLR-T24 WH
		Full product name	TBS528 1x49W HFP O FU TLR-T24 WH
Operating and Electrical		Order code	910403630666
Power Consumption	49 W	Material Nr. (12NC)	910403630666
Cable	-	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	2

## Intelligent Sereno TBS869/528

### Dimensional drawing

