



# Intelligent Sereno TBS869/528

## TBS528 1x54W HFP O FU MLK-T15 WH

1, 54 W, HF Performer, Opal, Fuse included, White

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Embedded control	-
Light Technical	
Number of light sources	1
Light source color	-
Optic type	-
Optical cover type	Opal
Operating and Electrical	
Power Consumption	54 W
Cable	-

Mechanical and Housing	
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	TBS528 1x54W HFP O FU MLK-T15 WH
Full product name	TBS528 1x54W HFP O FU MLK-T15 WH
Order code	910403630670
Material Nr. (12NC)	910403630670
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Intelligent Sereno TBS869/528

### Dimensional drawing

