



# Intelligent Sereno TBS869/528

## TBS869 C 1x28W HFP D8 FU TLR-T24 WH

1, 28 W, HF Performer, Semi-high-gloss optic 3D micro-lamellae, Fuse included, White

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

### Product data

General Information		Approval and Application	
Lamp family code	TL5 [TL5]	Ingress protection code	IP20 [Finger-protected]
Gear	HFP [HF Performer]		
Embedded control	-		
Light Technical		Product Data	
Number of light sources	1	Order product name	TBS869 C 1x28W HFP D8 FU TLR-T24 WH
Light source color	-	Full product name	TBS869 C 1x28W HFP D8 FU TLR-T24 WH
Optic type	Semi-high-gloss optic 3D micro-lamellae	Order code	910403630672
Operating and Electrical		Material Nr. (12NC)	910403630672
Power Consumption	28 W	Numerator - Quantity Per Pack	1
Cable	-	Numerator - Packs per outer box	2
Mechanical and Housing			
Housing Color	White		

## Intelligent Sereno TBS869/528

### Dimensional drawing

