



Intelligent Sereno TBS869/528

TBS869 C 1x35W HFP D8 FU WH

1, 35 W, HF Performer, Semi-high-gloss optic 3D micro-lamellae, Fuse included, White

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Embedded control	-
Light Technical	
Number of light sources	1
Light source color	-
Optic type	Semi-high-gloss optic 3D micro-lamellae
Operating and Electrical	
Power Consumption	35 W
Cable	-
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	TBS869 C 1x35W HFP D8 FU WH
Full product name	TBS869 C 1x35W HFP D8 FU WH
Order code	910403630680
Material Nr. (12NC)	910403630680
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291994473
Numerator - Packs per outer box	2
EAN/UPC - Case	8718291994473

Intelligent Sereno TBS869/528

Dimensional drawing

