



# Intelligent Sereno TBS869/528

## TBS869 C 1x54W HFP D8 FU WH

1, 54 W, HF Performer, Semi-high-gloss optic 3D micro-lamellae, Fuse included, White

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

### Product data

General Information		Approval and Application	
Lamp family code	TL5 [TL5]	Ingress protection code	IP20 [Finger-protected]
Gear	HFP [HF Performer]	Product Data	
Embedded control	-	Order product name	TBS869 C 1x54W HFP D8 FU WH
Light Technical		Full product name	TBS869 C 1x54W HFP D8 FU WH
Number of light sources	1	Order code	910403630687
Light source color	-	Material Nr. (12NC)	910403630687
Optic type	Semi-high-gloss optic 3D micro-lamellae	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	2
Power Consumption	54 W	Mechanical and Housing	
Cable	-	Housing Color	White
Mechanical and Housing			

## Intelligent Sereno TBS869/528

### Dimensional drawing

