



# Intelligent Sereno TBS869/528

## TBS528 3xTL5-14W HFA P FU

3, TL5, 14 W, HF standard for TL5, Opal prismatic cover, Fuse included

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

### Product data

| General Information      |                           | Mechanical and Housing          |                           |
|--------------------------|---------------------------|---------------------------------|---------------------------|
| Lamp family code         | TL5 [TL5]                 | Housing Color                   | White                     |
| Gear                     | HFA [HF standard for TL5] | Approval and Application        |                           |
| Embedded control         | -                         | Ingress protection code         | IP20 [Finger-protected]   |
| Light Technical          |                           | Product Data                    |                           |
| Number of light sources  | 3                         | Order product name              | TBS528 3xTL5-14W HFA P FU |
| Light source color       | -                         | Full product name               | TBS528 3xTL5-14W HFA P FU |
| Optic type               | -                         | Full product code               | 910403630689              |
| Optical cover type       | Opal prismatic cover      | Order code                      | 910403630689              |
| Operating and Electrical |                           | Material Nr. (12NC)             | 910403630689              |
| Power Consumption        | 14 W                      | Numerator - Quantity Per Pack   | 1                         |
| Cable                    | -                         | Numerator - Packs per outer box | 2                         |

Intelligent Sereno TBS869/528

Dimensional drawing

