



Intelligent Sereno TBS869/528

TBS528 2xTL5-28W HFA P FU

2, TL5, 28 W, HF standard for TL5, Opal prismatic cover, Fuse included

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	White
Gear	HFA [HF standard for TL5]		
Embedded control	-	Approval and Application	
		Ingress protection code	IP20 [Finger-protected]
Light Technical		Product Data	
Number of light sources	2	Order product name	TBS528 2xTL5-28W HFA P FU
Light source color	-	Full product name	TBS528 2xTL5-28W HFA P FU
Optic type	-	Full product code	910403630691
Optical cover type	Opal prismatic cover	Order code	910403630691
		Material Nr. (12NC)	910403630691
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	28 W	Numerator - Packs per outer box	2
Cable	-		

Intelligent Sereno TBS869/528

Dimensional drawing

