



Intelligent Sereno TBS869/528

TBS528 2xTL5-35W HFA M8 FU IPP

2, TL5, 35 W, HF standard for TL5, Matt optic 3D micro-lamellae,
Fuse included

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	White
Gear	HFA [HF standard for TL5]	Approval and Application	
Embedded control	-	Ingress protection code	IP20 [Finger-protected]
Light Technical		Product Data	
Number of light sources	2	Order product name	TBS528 2xTL5-35W HFA M8 FU IPP
Light source color	-	Full product name	TBS528 2xTL5-35W HFA M8 FU IPP
Optic type	Matt optic 3D micro-lamellae	Full product code	910403630694
Optical cover type	-	Order code	910403630694
Operating and Electrical		Material Nr. (12NC)	910403630694
Power Consumption	35 W	Numerator - Quantity Per Pack	1
Cable	-	Numerator - Packs per outer box	2

Intelligent Sereno TBS869/528

Dimensional drawing

