



# TCH086

## TCH086 TL5-21W/865 HF 110V TW

TL5, 21 W, 865 cool daylight, Electronic high-frequency, 127 V

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
Service tag	Yes
Light Technical	
Number of light sources	1
Light source color	865 cool daylight
Operating and Electrical	
Input Voltage	127 V
Line Frequency	50 to 60 Hz
Power Consumption	21 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class II
Product Data	
Order product name	TCH086 TL5-21W/865 HF 110V TW
Full product name	TCH086 TL5-21W/865 HF 110V TW
Full product code	910403630703
Order code	910403630703
Material Nr. (12NC)	910403630703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163289564
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163289687

## TCH086

### Dimensional drawing

