



Cozy TMS018 C

TMS018 C 2xTL-D36W EB R

2, MASTER TL-D, 36 W, Electronic, Reflector

Our Smart T8 Batten is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

Product data

| General Information | |
|--------------------------|-------------------------|
| Lamp family code | TL-D [MASTER TL-D] |
| Gear | EB [Electronic] |
| Light Technical | |
| Number of light sources | 2 |
| Optic type | Reflector |
| Operating and Electrical | |
| Input Voltage | 220 V |
| Line Frequency | 50 Hz |
| Power Consumption | 36 W |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |

| Protection class IEC | Safety class I |
|---------------------------------|-------------------------|
| Product Data | |
| Order product name | TMS018 C 2xTL-D36W EB R |
| Full product name | TMS018 C 2xTL-D36W EB R |
| Full product code | 910403630718 |
| Order code | 910403630718 |
| Material Nr. (12NC) | 910403630718 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 6923828602550 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 6923828602550 |

Cozy TMS018 C

Dimensional drawing

