



Basic Modular LBX300

LBX302 2xMAX50W/12V-GU5.3 SV GR

Grey

Our Smart Modular Downlight is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

Product data

General Information		Power Factor (Fraction)	
Light source replaceable	No	0.8	
Gear	-	Temperature	
Lighting Technology	LED	Ambient temperature range	
Light Technical		0 to +35 °C	
Luminous Flux	300 lm	Mechanical and Housing	
Correlated Color Temperature (Nom)	4000 K	Housing Material	
Color rendering index (CRI)	80	Plastic	
Light source color	3000/4000/6500	Reflector material	
Luminaire light beam spread	110°	Polycarbonate	
Operating and Electrical		Housing Color	
Line Frequency	50 or 60 Hz	Grey	
Input Frequency	50 or 60 Hz	Overall length	
Power Consumption	4 W	225 mm	
		Overall width	
		225 mm	
		Overall height	
		225 mm	
		Overall diameter	
		225 mm	
		Dimensions (Height x Width x Depth)	
		225 x 225 x 225 mm	
		Approval and Application	
		Ingress protection code	
		IP20 [Finger-protected]	

Basic Modular LBX300

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Product Data	
Order product name	LBX302 2xMAX50W/12V-GU5.3 SV GR
Full product name	LBX302 2xMAX50W/12V-GU5.3 SV GR
Full product code	910403630816
Order code	910403630816

Material Nr. (12NC)	910403630816
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828689162
Numerator - Packs per outer box	20
EAN/UPC - Case	6923828602109

Dimensional drawing

