



Basic Modular LBX300

LBX302 3xMAX50W/12V-GU5.3 RV GR

Grey

Our Smart Modular Downlight is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

Product data

General Information		Power Factor (Fraction)	
Light source replaceable	No	0.8	
Gear	-	Temperature	
Lighting Technology	LED	Ambient temperature range	
		0 to +35 °C	
Light Technical		Mechanical and Housing	
Luminous Flux	300 lm	Housing Material	Plastic
Correlated Color Temperature (Nom)	4000 K	Reflector material	Polycarbonate
Color rendering index (CRI)	80	Housing Color	Grey
Light source color	3000/4000/6500	Overall length	225 mm
Luminaire light beam spread	110°	Overall width	225 mm
		Overall height	225 mm
Operating and Electrical		Overall diameter	225 mm
Line Frequency	50 or 60 Hz	Dimensions (Height x Width x Depth)	225 x 225 x 225 mm
Input Frequency	50 or 60 Hz		
Power Consumption	4 W	Approval and Application	
		Ingress protection code	IP20 [Finger-protected]

Basic Modular LBX300

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Product Data	
Order product name	LBX302 3xMAX50W/12V-GU5.3 RV GR
Full product name	LBX302 3xMAX50W/12V-GU5.3 RV GR
Full product code	910403630823
Order code	910403630823

Material Nr. (12NC)	910403630823
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828689209
Numerator - Packs per outer box	10
EAN/UPC - Case	6923828602147

Dimensional drawing

