



PowerVision MVF024

MVF024 MHN-FC1000W/740 230V NB SI

POWERSVISION, MASTER MHN-FC, 1000 W, Narrow beam

PowerVision is a high-performance general-purpose floodlight for sports lighting, general area lighting and facade illumination. This compact luminaire distributes a low-glare, wide, medium or narrow beam evenly, accurately and efficiently. With the MHN-LA 2000W/842 lamp, the natural color rendering (Ra = 80) and comfortable atmosphere (Tc = 4200 K) are well suited to TV and filming. With the MHN-LA 2000W/956 lamp, the highest international CTV requirements (Ra = 90, Tc = 5600 K) are met. A built-in skirt in the reflector assembly minimizes spill light and glare. Integrated system of optics, gear and lamp in a single housing, ensuring high beam efficiency and a well-controlled beam. Built-in skirt in reflector assembly minimizes spill light and glare. The luminaire's rugged all-weather construction is designed for easy aiming, simple cleaning and speedy servicing.

Product data

General Information		Power Consumption	
Lamp family code	MHN-FC [MASTER MHN-FC]	1,000 W	
Gear	CONV [Conventional]	Mechanical and Housing	
Product family code	MVF024 [POWERSVISION]	Housing Color	
CE mark	Yes	-	
ENEC mark	ENEC mark	Approval and Application	
Light Technical		Ingress protection code	
Number of light sources	1	IP55 [Dust accumulation-protected, jet-proof]	
Light source color	740 neutral white	Protection class IEC	
Optic type outdoor	Narrow beam	Safety class I	
Operating and Electrical		Product Data	
Input Voltage	230 V	Order product name	
		MVF024 MHN-FC1000W/740 230V NB SI	
		Full product name	
		MVF024 MHN-FC1000W/740 230V NB SI	
		Full product code	
		872790029252700	
		Order code	
		910403758412	

PowerVision MVF024

Material Nr. (12NC)	910403758412
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900292527
Numerator - Packs per outer box	1

EAN/UPC - Case	8727900292527
----------------	---------------

Dimensional drawing

