



PowerVision MVF024

MVF024 MHN-FC1000W/740 230V MB SI

POWERVISION, MASTER MHN-FC, 1000 W, Medium beam

PowerVision is a high-performance general-purpose floodlight for sports lighting, general area lighting and facade illumination. This compact luminaire distributes a low-glare, wide, medium or narrow beam evenly, accurately and efficiently. With the MHN-LA 2000W/842 lamp, the natural color rendering (Ra = 80) and comfortable atmosphere (Tc = 4200 K) are well suited to TV and filming. With the MHN-LA 2000W/956 lamp, the highest international CTV requirements (Ra = 90, Tc = 5600 K) are met. A built-in skirt in the reflector assembly minimizes spill light and glare. Intergrated system of optics, gear and lamp in a single housing, ensuring high beam efficiency and a well-controlled beam. Built-in skirt in reflector assembly minimizes spill light and glare. The luminaire's rugged all-weather construction is designed for easy aiming, simple cleaning and speedy servicing.

Product data

General Information	
Lamp family code	MHN-FC [MASTER MHN-FC]
Gear	CONV [Conventional]
Product family code	MVF024 [POWERVISION]
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Number of light sources	1
Light source color	740 neutral white
Optic type outdoor	Medium beam
Operating and Electrical	
Input Voltage	230 V

Power Consumption	1,000 W
Mechanical and Housing	
Housing Color	-
Approval and Application	
Ingress protection code	IP55 [Dust accumulation-protected, jet-proof]
Protection class IEC	Safety class I
Product Data	
Order product name	MVF024 MHN-FC1000W/740 230V MB SI
Full product name	MVF024 MHN-FC1000W/740 230V MB SI
Full product code	872790029253400
Order code	29253400

PowerVision MVF024

Material Nr. (12NC)	910403758512
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900292534
Numerator - Packs per outer box	1

EAN/UPC - Case	8727900292534
----------------	---------------

Dimensional drawing

