



# OptiVision MVP507

## MVP507 MHN-FC2000W/740 400V MB SI SL

OPTIVISION, MASTER MHN-FC, 2000 W, Medium beam

Optivision is an asymmetric downlighting luminaire that combines compact dimensions with very high efficiency. Available with narrow, medium and wide beams for flexibility in application, it provides excellent control of spill light and limitation of glare and upward leakage of light. Optivision can accommodate metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Excellent spill-light control, limitation of glare and upward leakage of light is secured by asymmetric optics that achieve peak intensity at 60° and a sharp cut-off of light at 80°. The MHN-LA/FC lamps guarantee pleasant and natural color rendering and comfortable atmosphere.

### Product data

General Information		Operating and Electrical	
Lamp family code	MHN-FC [MASTER MHN-FC]	Color rendering index (CRI)	>70
Number of gear units	-	Number of light sources	1
Gear	-	Light source color	740 neutral white
Product family code	MVP507 [OPTIVISION]	Optical cover type	Flat glass
Value ladder	Specification	Luminaire light beam spread	-
CE mark	Yes	Optic type outdoor	Medium beam
Warranty period	1 years		
Flammability mark	-	Input Voltage	400 V
ENEC mark	-	Line Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power Consumption	2,000 W
		Connection	Screw connector
		Cable	-
Light Technical			
Standard tilt angle posttop	-		
Standard tilt angle side entry	-		
Correlated Color Temperature (Nom)	4000 K		

OptiVision MVP507

Temperature	
Ambient temperature range	-30 to +35 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	Aluminum
Optic material	Aluminum
Optical cover material	-
Fixation material	Steel
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	-
Overall height	386 mm
Effective projected area	0.16 m²
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	-
Sustainability rating	-
Protection class IEC	Safety class I
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	MVP507 MHN-FC2000W/740 400V MB SI SL
Full product name	MVP507 MHN-FC2000W/740 400V MB SI SL
Full product code	872790029716400
Order code	910403788212
Material Nr. (12NC)	910403788212
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900297164
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900297164

Dimensional drawing

