



OptiFlood MVP506

MVP506 CDM-TMW210W/930 EB OR

OptiFlood, MASTERColour CDM-T Elite MW, 210 W, Electronic, Open CT-POT

Philips has a long tradition of excellence in environmentally friendly asymmetric floodlighting systems for sports and general area lighting as well as architectural applications. OptiFlood's extremely efficient, best-in-class optical system provides an accurately controlled light distribution – total light cut-off above the horizontal and a peak beam intensity at high angles – keeping obtrusive light to a minimum. Both the MVP504 and MVP506 versions are available with two types of reflector – asymmetric or road-lighting POT optics – for flexibility in application. They can also accommodate CosmoPolis metal-halide lamps for good color rendering, high-pressure sodium lamps for economical operation, and MASTERColour CDM Elite MW lamps for highly efficient lighting with longer-lasting white light. OptiFlood is also available in a LED version (BVP506). With its compact shape and aesthetically pleasing design, OptiFlood can be used in applications where design and appearance are just as important as technical performance. In the design, attention has also been focused on the detailing. This has led to integrated 'hidden' hinges, angle adjustment designed as part of the body and a mounting bracket angled to allow more aesthetic integration onto columns.

Product data

General Information		Light Technical	
Lamp family code	CDM-TMW [MASTERColour CDM-T Elite MW]	Light source colour	930 warm white
Gear	EB [Electronic]	Optical cover type	Flat glass
Product family code	MVP506 [OptiFlood]	Optic type outdoor	Open CT-POT
CE mark	Yes	Operating and Electrical	
ENEC mark	ENEC mark	Input Voltage	220 to 240 V
Glow-wire test	Temperature 850 °C, duration 5 s		

OptiFlood MVP506

Power Consumption	210 W
Mechanical and Housing	
Housing Colour	Aluminium
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Protection class IEC	Safety class I
Product Data	
Order product name	MVP506 CDM-TMW210W/930 EB OR

Full product name	MVP506 CDM-TMW210W/930 EB OR
Full EOC	872790029655600
Order code	29655600
Material no. (12 NC)	910403791312
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900296556
Numerator – packs per outer box	1
EAN/UPC – Case	8727900296556

Dimensional drawing

