



# OptiFlood MVP506

## MVP506 CDM-TMW315W/942 EB A

OptiFlood, MASTERColour CDM-T Elite MW, 315 W, Electronic, Asymmetrical

Philips has a long tradition of excellence in environmentally friendly asymmetric floodlighting systems for sports and general area lighting as well as architectural applications. OptiFlood's extremely efficient, best-in-class optical system provides an accurately controlled light distribution – total light cut-off above the horizontal and a peak beam intensity at high angles – keeping obtrusive light to a minimum. Both the MVP504 and MVP506 versions are available with two types of reflector – asymmetric or road-lighting POT optics – for flexibility in application. They can also accommodate CosmoPolis metal-halide lamps for good color rendering, high-pressure sodium lamps for economical operation, and MASTERColour CDM Elite MW lamps for highly efficient lighting with longer-lasting white light. OptiFlood is also available in a LED version (BVP506). With its compact shape and aesthetically pleasing design, OptiFlood can be used in applications where design and appearance are just important as technical performance. In the design, attention has also been focused on the detailing. This has led to integrated 'hidden' hinges, angle adjustment designed as part of the body and a mounting bracket angled to allow more aesthetic integration onto columns.

### Product data

General Information	
Lamp family code	CDM-TMW [MASTERColour CDM-T Elite MW]
Gear	EB [Electronic]
Product family code	MVP506 [OptiFlood]
CE mark	Yes
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s

Light Technical	
Light source colour	942 neutral white
Optical cover type	Flat glass
Optic type outdoor	Asymmetrical

  

Operating and Electrical	
Input Voltage	220 to 240 V

# OptiFlood MVP506

<b>Power Consumption</b>	315 W
<b>Mechanical and Housing</b>	
<b>Housing Colour</b>	Aluminium
<b>Approval and Application</b>	
<b>Ingress protection code</b>	IP66 [Dust penetration-protected, jet-proof]
<b>Mech. impact protection code</b>	IK09 [10 J]
<b>Protection class IEC</b>	Safety class I

## Product Data

<b>Order product name</b>	MVP506 CDM-TMW315W/942 EB A
---------------------------	-----------------------------

<b>Full product name</b>	MVP506 CDM-TMW315W/942 EB A
<b>Full EOC</b>	872790029985400
<b>Order code</b>	29985400
<b>Material no. (12 NC)</b>	910403803212
<b>SAP numerator – quantity per pack</b>	1
<b>EAN/UPC – Product/Case</b>	8727900299854
<b>Numerator – packs per outer box</b>	1
<b>EAN/UPC – Case</b>	8727900299854

## Dimensional drawing

