



# ComfortVision SNF111

## SNF111 2XSON-T600W K NB SI RAL9006

COMFORTVISION, 2, SON-T, 600 W, Narrow beam

ComfortVision is a high-efficiency, asymmetric floodlight, distributing a low-glare beam evenly and accurately. It can accommodate metal-halide lamps for good color rendering or a high-pressure sodium lamp for economical performance. Available in medium- or narrow-beam versions, the floodlight accepts a single 1000 or two 400 or 600 W lamps. The twin-lamp version offers switching flexibility that permits tailoring to the user's needs while allowing energy savings. ComfortVision's rugged all-weather construction is designed for easy aiming, simple cleaning and speedy servicing. For optimal downlighting, the luminaire should be mounted horizontally at a height of 15–25 meters. It has an adjustment range of  $\pm 12^\circ$  from the horizontal. A universal mounting bracket allows mounting to headframes, ceilings and walls.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Product family code	SNF111 [COMFORTVISION]
CE mark	Yes
ENEC mark	-
Light Technical	
Number of light sources	2
Optic type outdoor	Narrow beam
Operating and Electrical	
Power Consumption	600 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Protection class IEC	Safety class I
Product Data	
Order product name	SNF111 2XSON-T600W K NB SI RAL9006
Full product name	SNF111 2XSON-T600W K NB SI RAL9006
Full product code	871829142133700
Order code	910403970112
Material Nr. (12NC)	910403970112
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291421337
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291421337

### Dimensional drawing

