



Europa 2

FBS120 2XPL-C/4P18W/840 HF-H P CW2

TurnRound Projector, 2, MASTER PL-C 4 Pin, 18 W, 840 neutral white, Electronic high-frequency in external gear box (HF), Prismatic refractor, Cord with plug Wieland/Adels compatible 2-pole

Europa 2 is a fixed recessed downlight for compact fluorescent PL-C lamps with highly efficient optics and automatic fixing clips for quick and easy installation. These downlights are available in two formats and can be fitted with a prismatic light control panel, opal cover, clear front panel or glare-control louver. Europa 2 is available in a ready-to-install kit version.

Product data

General Information		Operating and Electrical	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]	Input Voltage	220 to 240 V
Gear	HF-H [Electronic high-frequency in external gear box (HF)]	Power Consumption	18 W
Product family code	BRG394 [TurnRound Projector]	Connection	-
CE mark	Yes	Cable	Cord with plug Wieland/Adels compatible 2-pole
Flammability mark	For mounting on normally flammable surfaces	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP20 [Finger-protected]
Glow-wire test	Temperature 850 °C, duration 5 s	Protection class IEC	Safety class II
Light Technical		Application Conditions	
Number of light sources	2	Suitable for random switching	Not applicable
Light source color	840 neutral white	Product Data	
Optic type	-	Order product name	FBS120 2XPL-C/4P18W/840 HF-H P CW2
Optical cover type	Prismatic refractor	Full product name	FBS120 2XPL-C/4P18W/840 HF-H P CW2

Europa 2

Full product code	871829108592800
Order code	08592800
Material Nr. (12NC)	910500451715
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291085928

Numerator - Packs per outer box 1	
EAN/UPC - Case	8718291085928

Dimensional drawing

