



# Europa 2

## FBS120 2XPL-C/4P18W/840 HF-H PG CW3

TurnRound Projector, 2, MASTER PL-C 4 Pin, 18 W, 840 neutral white, Electronic high-frequency in external gear box (HF), Protection glass, Cord with plug Wieland/Adels compatible 3-pole

Europa 2 is a fixed recessed downlight for compact fluorescent PL-C lamps with highly efficient optics and automatic fixing clips for quick and easy installation. These downlights are available in two formats and can be fitted with a prismatic light control panel, opal cover, clear front panel or glare-control louver. Europa 2 is available in a ready-to-install kit version.

### Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	HF-H [Electronic high-frequency in external gear box (HF)]
Product family code	BRG394 [TurnRound Projector]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	-
Optical cover type	Protection glass

Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	18 W
Connection	-
Cable	Cord with plug Wieland/Adels compatible 3-pole
Approval and Application	
Ingress protection code	IP44 [Wire-protected, splash-proof]
Protection class IEC	Safety class II
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	FBS120 2XPL-C/4P18W/840 HF-H PG CW3
Full product name	FBS120 2XPL-C/4P18W/840 HF-H PG CW3

Europa 2

Full product code	871829108596600
Order code	08596600
Material Nr. (12NC)	910500451719
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291085966

Numerator - Packs per outer box 1	
EAN/UPC - Case	8718291085966

Dimensional drawing

