



# Europa 2

## FBS120 2XPL-C/4P26W/830 HF-H PG CW3

EUROPA 2, 2, MASTER PL-C 4 Pin, 26 W, 830 warm white, Electronic high-frequency in external gear box (HF), Protection glass, Cord with plug Wieland/Adels compatible 3-pole

Europa 2 is a fixed recessed downlight for compact fluorescent PL-C lamps with highly efficient optics and automatic fixing clips for quick and easy installation. These downlights are available in two formats and can be fitted with a prismatic light control panel, opal cover, clear front panel or glare-control louver. Europa 2 is available in a ready-to-install kit version.

### Product data

General Information		Operating and Electrical	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]	Input Voltage	220 to 240 V
Gear	HF-H [Electronic high-frequency in external gear box (HF)]	Power Consumption	26 W
Product family code	FBS120 [EUROPA 2]	Connection	-
CE mark	Yes	Cable	Cord with plug Wieland/Adels compatible 3-pole
Flammability mark	For mounting on normally flammable surfaces	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP44 [Wire-protected, splash-proof]
Glow-wire test	Temperature 850 °C, duration 5 s	Protection class IEC	Safety class II
Light Technical		Application Conditions	
Number of light sources	2	Suitable for random switching	Not applicable
Light source color	830 warm white	Product Data	
Optic type	-	Order product name	FBS120 2XPL-C/4P26W/830 HF-H PG CW3
Optical cover type	Protection glass	Full product name	FBS120 2XPL-C/4P26W/830 HF-H PG CW3
		Full product code	871829108608600

## Europa 2

Order code	910500451731
Material Nr. (12NC)	910500451731
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291086086

Numerator - Packs per outer box	1
EAN/UPC - Case	8718291086086

### Dimensional drawing

