



Europa 2

FBS120 2XPL-C/4P26W/830 HF-H PG CCE

EUROPA 2, 2, MASTER PL-C 4 Pin, 26 W, 830 warm white, Electronic high-frequency in external gear box (HF), Protection glass, Cable with CEE 7 plug 3-pole

Europa 2 is a fixed recessed downlight for compact fluorescent PL-C lamps with highly efficient optics and automatic fixing clips for quick and easy installation. These downlights are available in two formats and can be fitted with a prismatic light control panel, opal cover, clear front panel or glare-control louver. Europa 2 is available in a ready-to-install kit version.

Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	HF-H [Electronic high-frequency in external gear box (HF)]
Product family code	FBS120 [EUROPA 2]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	2
Light source color	830 warm white
Optic type	-
Optical cover type	Protection glass

Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	26 W
Connection	-
Cable	Cable with CEE 7 plug 3-pole

Approval and Application	
Ingress protection code	IP44 [Wire-protected, splash-proof]
Protection class IEC	Safety class II

Application Conditions	
Suitable for random switching	Not applicable

Product Data	
Order product name	FBS120 2XPL-C/4P26W/830 HF-H PG CCE
Full product name	FBS120 2XPL-C/4P26W/830 HF-H PG CCE
Full product code	871829108609300

Europa 2

Order code	08609300
Material Nr. (12NC)	910500451732
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291086093

Numerator - Packs per outer box	1
EAN/UPC - Case	8718291086093

Dimensional drawing

