



# Europa 2

## FBS120 2XPL-C/4P26W/840 HF-H P CW3

EUROPA 2, 2, MASTER PL-C 4 Pin, 26 W, 840 neutral white, Electronic high-frequency in external gear box (HF), Prismatic refractor, Cord with plug Wieland/Adels compatible 3-pole

Europa 2 is a fixed recessed downlight for compact fluorescent PL-C lamps with highly efficient optics and automatic fixing clips for quick and easy installation. These downlights are available in two formats and can be fitted with a prismatic light control panel, opal cover, clear front panel or glare-control louver. Europa 2 is available in a ready-to-install kit version.

### Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	HF-H [Electronic high-frequency in external gear box (HF)]
Product family code	FBS120 [EUROPA 2]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	-
Optical cover type	Prismatic refractor

Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	26 W
Connection	-
Cable	Cord with plug Wieland/Adels compatible 3-pole

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class II

Application Conditions	
Suitable for random switching	Not applicable

Product Data	
Order product name	FBS120 2XPL-C/4P26W/840 HF-H P CW3
Full product name	FBS120 2XPL-C/4P26W/840 HF-H P CW3
Full product code	871829108614700

Europa 2

Order code	910500451737
Material Nr. (12NC)	910500451737
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291086147

Numerator - Packs per outer box 1	
EAN/UPC - Case	8718291086147

Dimensional drawing

