



GreenSpace

DN460B LED11S/840 PSED-E C WH CU5 PGO

150mm, LED Module, system flux 1100 lm, 840 neutral white, Power supply unit with DALI interface, DC compatible, external, Connection unit 5-pole, Wire-protected, splash-proof, White RAL 9003

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable color performance and high color rendering. The product’s long lifetime makes it a true ‘fit and forget’ solution.

Product data

General Information			
Lamp family code	LED11S [LED Module, system flux 1100 lm]	Product family code	DN460B [150mm]
Cap-Base	- [-]	Lighting Technology	LED
Light source replaceable	No	Value ladder	Specification
Number of gear units	1 unit	CE mark	Yes
Gear	-	Warranty period	3 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	1,100 lm
		Correlated Color Temperature (Nom)	4000 K

Luminous Efficacy (rated) (Nom)	104 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	High-gloss mirror
Luminaire light beam spread	80°
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	16 A
Inrush time	0.22 ms
Power Consumption	10.6 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall height	77 mm

Overall diameter	166 mm
------------------	--------

Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	DN460B LED11S/840 PSED-E C WH CU5 PGO
Full product name	DN460B LED11S/840 PSED-E C WH CU5 PGO
Full product code	871869624662700
Order code	24662700
Material Nr. (12NC)	910500456250
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696246627
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696246627

Dimensional drawing

