



# GreenSpace

## DN461B LED11S/840 PSE-E C WH CU3

150mm + anti-glare ring, LED Module, system flux 1100 lm, 840 neutral white, Power supply unit DC compatible, external, Connection unit 3-pole, White RAL 9003

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable color performance and high color rendering. The product's long lifetime makes it a true 'fit and forget' solution.

### Product data

General Information		Lighting Technology	
Lamp family code	LED11S [LED Module, system flux 1100 lm]	Value ladder	Specification
Cap-Base	- [-]	CE mark	Yes
Light source replaceable	No	Warranty period	3 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Gear	-	ENEC mark	ENEC mark
Driver included	Yes	Glow-wire test	Temperature 850 °C, duration 5 s
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	Yes
Product family code	DN461B [150mm + anti-glare ring]	Light Technical	
		Luminous Flux	1,200 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	113 lm/W
		Color rendering index (CRI)	80

Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	High-gloss mirror
Luminaire light beam spread	66°
Unified glare rating CEN	22

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14 A
Inrush time	0.24 ms
Power Consumption	10.6 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type B	30

#### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	-
Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	-
Overall height	77 mm

Overall diameter	166 mm
------------------	--------

#### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-5%

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

#### Product Data

Order product name	DN461B LED11S/840 PSE-E C WH CU3
Full product name	DN461B LED11S/840 PSE-E C WH CU3
Full product code	871869624664100
Order code	24664100
Material Nr. (12NC)	910500456252
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696246641
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696246641

#### Dimensional drawing



