



GreenSpace

DN470B LED20S/840 PSE-E C WH PGO

200mm, LED Module, system flux 2000 lm, 840 neutral white, Power supply unit DC-compatible, external, Wire-protected, splash-proof, White RAL 9003

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable colour performance and high colour rendering. The product's long lifetime makes it a true 'fit and forget' solution.

Product data

General Information	
Lamp family code	LED20S [LED Module, system flux 2000 lm]
Cap base	- [-]
Light source replaceable	No
Number of gear units	Unit
Gear	-
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.

Product family code	DN470B [200mm]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical	
Luminous Flux	2,200 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	118.28 lm/W

Colour rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	High-gloss mirror
Luminaire light beam spread	88°
Unified Glare Rating (CEN)	25

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14 A
Inrush time	0.24 ms
Power Consumption	18.6 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	30

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC-compatible, external
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Glass
Fixation material	-
Housing Colour	White RAL 9003
Optical cover/lens finish	Frosted
Overall height	95 mm

Overall diameter	216 mm
------------------	--------

Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	DN470B LED20S/840 PSE-E C WH PGO
Full product name	DN470B LED20S/840 PSE-E C WH PGO
Full EOC	871869624676400
Order code	24676400
Material no. (12 NC)	910500456264
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696246764
Numerator – packs per outer box	1
EAN/UPC - Case	8718696246764

Dimensional drawing



