



GreenSpace

DN470B LED20S/830 PSED-E C WH CU5 GC

200mm, LED Module, system flux 2000 lm, 830 warm white, Power supply unit with DALI interface, DC compatible, external, Connection unit 5-pole, Wire-protected, splash-proof, White RAL 9003

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable color performance and high color rendering. The product's long lifetime makes it a true 'fit and forget' solution.

Product data

General Information			
Lamp family code	LED20S [LED Module, system flux 2000 lm]	Product family code	DN470B [200mm]
Cap-Base	- [-]	Lighting Technology	LED
Light source replaceable	No	Value ladder	Specification
Number of gear units	1 unit	CE mark	Yes
Gear	-	Warranty period	3 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	2,050 lm
		Correlated Color Temperature (Nom)	3000 K

Luminous Efficacy (rated) (Nom)	112 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	High-gloss mirror
Luminaire light beam spread	88°
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	16 A
Inrush time	0.22 ms
Power Consumption	18.3 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	Clear

Overall height	95 mm
Overall diameter	216 mm

Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44, 0.40) SDCM<3
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	DN470B LED20S/830 PSED-E C WH CU5 GC
Full product name	DN470B LED20S/830 PSED-E C WH CU5 GC
Full product code	871869624693100
Order code	24693100
Material Nr. (12NC)	910500456281
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696246931
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696246931

Dimensional drawing

