



# Maxos LED Spot Inserts

## 4MX960 2 ST540C LED25S/830 PSU MB WH

MAXOS LED Spot Inserts, LED module, system flux 2500 lm, 830 warm white, Power supply unit (On/Off), Medium beam, White

In specific areas of shops such as fruit and vegetable displays, projectors are often required in addition to LED-based general lighting. Accent lighting is an integral part of the Maxos concept. These dedicated inserts allow light lines to be flexibly equipped with the latest range of projectors as well as general LED lighting. 4MX960 units with projectors for Maxos trunkings with flat ribbon cable (5 x 2.5 mm, 7 x 2.5 mm) are available. These units can be clicked into the trunking sections like a regular electrical unit. Surface-mounted projectors are fixed to the inserts.

### Product data

General Information	
Lamp family code	LED25S [LED module, system flux 2500 lm]
Remarks	* -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Product family code	4MX960 [MAXOS LED Spot Inserts]
Lighting Technology	LED
CE mark	Yes

Light Technical	
Luminous Flux	5,400 lumen
Correlated Color Temperature (Nom)	3000 K
Light source color	830 warm white
Optic type	Medium beam
Unified glare rating CEN	Not applicable
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

# Maxos LED Spot Inserts

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)

## Mechanical and Housing

Housing Color	White
---------------	-------

## Approval and Application

Protection class IEC	Safety class I
----------------------	----------------

## Application Conditions

Performance ambient temperature	25 °C
Tq	
Suitable for random switching	Not applicable

## Product Data

Full product code	871869625546900
Order product name	4MX960 2 ST540C LED25S/830 PSU MB WH
Order code	910500456571
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910500456571
Full product name	4MX960 2 ST540C LED25S/830 PSU MB WH
EAN/UPC - Case	8718696255469
EAN/UPC - Product/Case	8718696255469

## Dimensional drawing

