



StyliD

ST730T LED12S/827 PSU MB WH

STYLID MINI G3 TRACK, LED module, system flux 1200 lm, 827 warm white, Power supply unit, DC-compatible for central emergency lighting, Medium beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, StyliD is the ideal energy-efficient solution for today's demanding retail environments, covering a variety of lighting applications, with including CrispWhite for fashion stores and Food recipes for supermarkets.

Product data

General Information	
Lamp family code	LED12S [LED module, system flux 1200 lm]
Cap base	- [-]
Light source replaceable	No
Number of gear units	Unit
Gear	-
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10.

	Therefore, the median useful life (B50) value also represents the B10 value.
Product family code	ST730T [STYLID MINI G3 TRACK]
Lighting Technology	LED
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical	
Luminous Flux	1,150 lm

StyliD

Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	109.52380952380952 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	827 warm white
Optic type	Medium beam
Optical cover type	-
Luminaire light beam spread	30°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14 A
Inrush time	0.25 ms
Power Consumption	10.2 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit, DC-compatible for central emergency lighting
Constant light output	No

Mechanical and Housing

Housing material	Metal-Plastic
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Clear

Overall length	258 mm
Overall width	73 mm
Overall height	159 mm
Dimensions (height x width x depth)	159 x 73 x 258 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.45, 0.41) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	ST730T LED12S/827 PSU MB WH
Full product name	ST730T LED12S/827 PSU MB WH
Full EOC	871869684829600
Order code	84829600
Material no. (12 NC)	910500457352
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696848296
Numerator – packs per outer box	1
EAN/UPC - Case	8718696848296

Dimensional drawing



