



StyliD

ST740T LED27S/930 PSU MB BK

STYLID COMPACT G3 TRACK, LED Module, system flux 2700 lm, 930 warm white, Power supply unit, DC compatible for central emergency lighting, Medium beam, Black

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, StyliD is the ideal energy-efficient solution for today's demanding retail environments, covering a variety of lighting applications, with including CrispWhite for fashion stores and Food recipes for supermarkets.

Product data

General Information		Lighting Technology	
Lamp family code	LED27S [LED Module, system flux 2700 lm]	CE mark	Yes
Light source replaceable	No	Warranty period	5 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 30 s
Product family code	ST740T [STYLID COMPACT G3 TRACK]	EU RoHS compliant	Yes
Light Technical			
Luminous Flux		2,700 lm	
Correlated Color Temperature (Nom)		3000 K	
Luminous Efficacy (rated) (Nom)		105.88235294117646 lm/W	
Color rendering index (CRI)		≥90	

Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	930 warm white
Optic type	Medium beam
Optical cover type	-
Luminaire light beam spread	24°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14.5 A
Inrush time	0.22 ms
Power Consumption	25.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	32

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit, DC compatible for central emergency lighting
Constant light output	No

Mechanical and Housing

Housing Material	Metal–Plastic
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate
Fixation material	-
Housing Color	Black
Optical cover finish	Clear
Overall length	258 mm

Overall width	89 mm
Overall height	179 mm
Dimensions (Height x Width x Depth)	179 x 89 x 258 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	ST740T LED27S/930 PSU MB BK
Full product name	ST740T LED27S/930 PSU MB BK
Full product code	871869684839500
Order code	84839500
Material Nr. (12NC)	910500457362
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696848395
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696848395

Dimensional drawing



