



EcoStyle

ST440T LED19S/FMT PSU WB WH

EcoStyle track mounting, LED module, system flux 1900 lm, Fresh meat, Power supply unit (On/Off), Wide beam, Safety class II, White

Retailers are looking for an affordable LED accent-lighting solution with a reasonable payback compared to conventional technologies. Now, thanks to EcoStyle, they need look no further. With a LED light source and dedicated reflector system, EcoStyle delivers powerful, good-quality accent lighting, enabling retailers to display their merchandise in the best possible light. For food and fashion retailers, EcoStyle is available with special light recipes to further enhance the store ambiance and to show the produce and goods on offer in the very best light: Fresh Food Champagne is the perfect LED solution for displaying fruit, vegetables, cheese, bread and pastries in a warm lighting ambiance; Fresh Food Meat creates the best light setting for meat enhancement in a cool natural ambiance; CrispWhite is the clear choice for fashion retailers to make colors appear rich and intense while keeping whites bright. The track-mounted EcoStyle is also available in a choice of black or white finish. And the combination of efficient LED technology and an innovative heatsink ensures that this is a reliable, lasting solution.

Product data

General Information	
Lamp family code	LED19S [LED module, system flux 1900 lm]
Cap-Base	- [-]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based

luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Service tag	Yes
Product family code	ST440T [EcoStyle track mounting]
Lighting Technology	LED

CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	1,900 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	Fresh meat
Optic type	Wide beam
Optical cover type	Acrylic bowl/cover clear
Luminaire light beam spread	36°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	~ W
Inrush current	12.8 A
Inrush time	208 ms
Power Consumption	22 W
Power Factor (Fraction)	0.95
Connection	-
Cable	-
Number of products on MCB of 16 A type B	50

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
------------------	----------

Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate
Fixation material	Polyamide
Housing Color	White
Optical cover finish	Clear
Overall length	230 mm
Overall width	112 mm
Overall height	194 mm
Dimensions (Height x Width x Depth)	194 x 112 x 230 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.40, 0.33) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	No

Product Data

Order product name	ST440T LED19S/FMT PSU WB WH
Full product name	ST440T LED19S/FMT PSU WB WH
Full product code	871869685340500
Order code	910500457932
Material Nr. (12NC)	910500457932
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696853405
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696853405

Dimensional drawing

