



CoreLine Downlight

DN131B LED20S/830 PSU IP44 PI6 ALU

CoreLine Downlight ALU, LED Module, system flux 2000 lm, 830 warm white, Power supply unit (On/Off), Wire-protected, splash-proof, Push-in connector 6-pole, Aluminium

The CoreLine Downlight range of recessed luminaires is designed to replace CFL-ni/CFL-i based downlight luminaires. Their attractive TCO helps customers to make the switch to LED. These luminaires create a natural lighting effect for use in general lighting applications. They also deliver instant energy savings and have a much longer lifetime, creating a real value-for-money and environmentally friendly solution. They are easy to install thanks to their standard cut-out size and push-in connectors.

Product data

General Information	
Lamp family code	LED20S [LED Module, system flux 2000 lm]
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Product family code	DN131B [CoreLine Downlight ALU]
Lighting Technology	LED

Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	2,100 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	95 lm/W
Colour rendering index (CRI)	80
Beam angle of light source	120 degree(s)

CoreLine Downlight

Light source colour	830 warm white
Optic type	Wide beam
Optical cover type	Acrylic bowl/cover frosted
Luminaire light beam spread	60°
Unified Glare Rating (CEN)	25

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	16 A
Inrush time	0.32 ms
Power Consumption	22 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB of 16 A type B	15

Temperature

Ambient temperature range	-10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Aluminium
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	Aluminium
Optical cover/lens finish	Frosted
Overall height	109 mm

Overall diameter	216 mm
------------------	--------

Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L70


Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	DN131B LED20S/830 PSU IP44 PI6 ALU
Full product name	DN131B LED20S/830 PSU IP44 PI6 ALU
Full EOC	871869687893400
Order code	87893400
Material no. (12 NC)	910500458090
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696878934
Numerator – packs per outer box	1
EAN/UPC – Case	8718696878934

Dimensional drawing



CoreLine Downlight

