



# StoreFlux gen3 rim

## GD603B LED17S/830 PSU-E MB WH-WH

StoreFlux3, LED module, system flux 1700 lm, 830 warm white, Power supply unit external (On/Off), Medium beam, White and white

With StoreFlux, retailers can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in a refined and neutral product design that nicely blends in store architecture. The StoreFlux gridlight can be equipped with up to three LED modules with PerfectAccent reflector system to deliver top-quality accent lighting that makes your shop and merchandise look great. StoreFlux, next to long service lifetime, also offers tool-free reflector replacement and easy access to driver for hassle free maintenance.

### Warnings and Safety

- The luminaire should be mounted outside of arm's reach. Manipulating the product when hot is only possible with an insulated glove
- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements
- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- In case of no front glass lens, cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For areas with high levels of dust, the use of the optional front glass is strongly advised, as it can then be easily cleaned with a (dry) microfiber cloth
- For multi-spot configurations, please use single configuration photometry and duplicate it as per the number of spots in given configuration.

### Product data

General Information		Number of gear units	
Lamp family code	LED17S [LED module, system flux 1700 lm]	Driver included	3 units
Light source replaceable	No		Yes

## StoreFlux gen3 rim

Remarks	*-Per Lighting Europe guidance paper “Evaluating performance of LED based luminaires - January 2018”: statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Product family code	GD603B [StoreFlux3]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	5,100 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	118.05555555555556 lm/W
Color rendering index (CRI)	≥80
Number of light sources	3
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Medium beam
Optical cover type	Acrylic toothed
Luminaire light beam spread	22°
Unified glare rating CEN	Not applicable

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	6.1 A
Inrush time	0.31 ms
Power Consumption	13.8 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	34

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)

Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White and white
Optical cover finish	Clear
Overall length	473 mm
Overall width	179 mm
Overall height	165 mm
Dimensions (Height x Width x Depth)	165 x 179 x 473 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No

### Product Data

Order product name	GD603B LED17S/830 PSU-E MB WH-WH
Full product name	GD603B LED17S/830 PSU-E MB WH-WH
Full product code	871869688425600
Order code	910500458296
Material Nr. (12NC)	910500458296
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696884256
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696884256

StoreFlux gen3 rim

Dimensional drawing

