



StoreFlux gen3 rimless

GD614B LED20S/830 PSU-E CLI NB WH-WH

StoreFlux3, LED Module, system flux 2000 lm, 830 warm white, Power supply unit external (On/Off), Narrow beam, Safety class II, White and white

The StoreFlux gridlight can be equipped with up to three LED modules with a special reflector system to deliver top-quality light that makes your shop and merchandise look great. The combination of multiple LED sources with high lumen packages in one luminaire creates sparkling light effects. StoreFlux offers low maintenance compared with CDM and high efficiency compared to halogen.

Product data

General Information		Light Technical	
Lamp family code	LED20S [LED Module, system flux 2000 lm]	CE mark	Yes
Light source replaceable	No	Warranty period	5 years
Number of gear units	4 units	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 5 s
Product family code	GD614B [StoreFlux3]	EU RoHS compliant	Yes
Lighting Technology	LED	Luminous Flux	2,000 lm
Value ladder	Specification	Correlated Color Temperature (Nom)	3000 K
		Luminous Efficacy (rated) (Nom)	95 lm/W
		Color rendering index (CRI)	≥80
		Number of light sources	4
		Beam angle of light source	120 degree(s)

StoreFlux gen3 rimless

Light source color	830 warm white
Optic type	Narrow beam
Optical cover type	Clear glass
Luminaire light beam spread	10°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	6.1 A
Inrush time	0.31 ms
Power Consumption	21 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	34

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Steel
Housing Color	White and white

Optical cover finish	Clear
Overall length	588 mm
Overall width	147 mm
Overall height	165 mm
Dimensions (Height x Width x Depth)	165 x 147 x 588 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No

Product Data

Order product name	GD614B LED20S/830 PSU-E CLI NB WH-WH
Full product name	GD614B LED20S/830 PSU-E CLI NB WH-WH
Full product code	871869691037500
Order code	910500458432
Material Nr. (12NC)	910500458432
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696910375
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696910375

Dimensional drawing



StoreFlux gen3 rimless

