



ProAir

ST640T G2 LED39S/PW9 PSU WB WH

ProAir, Generation 2, LED Module, system flux 3900 lm,
Premium white with CRI ≥90, Power supply unit (On/Off), Wide
beam, White

Store designers want a spot that fits in with their store design. Visual merchandisers need the very best light quality and spots that are easily adjustable. And maintenance managers and green champions want to reduce energy consumption and maintenance costs. ProAir offers store designers a LED spot with an elegant and compact design that they can customize to suit their needs. It gives visual merchandisers great rendering of colors and whites and excellent color consistency, as well as well-defined, clean beams for maximum impact. All versions of ProAir offer low maintenance and energy consumption.

Product data

General Information			
Lamp family code	LED39S [LED Module, system flux 3900 lm]	CE mark	Yes
Light source replaceable	No	Warranty period	5 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 5 s
Product family code	ST640T [ProAir]	EU RoHS compliant	Yes
Lighting Technology	LED	Light Technical	
		Luminous Flux	3,900 lm
		Correlated Color Temperature (Nom)	3000 K
		Luminous Efficacy (rated) (Nom)	92 lm/W
		Color rendering index (CRI)	≥90
		Number of light sources	1
		Beam angle of light source	120 degree(s)

Light source color	Premium white with CRI ≥90
Optic type	Wide beam
Optical cover type	-
Luminaire light beam spread	33°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.250 ms
Power Consumption	42.5 W
Power Factor (Fraction)	0.9
Connection	-
Cable	-
Number of products on MCB of 16 A type B	30

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate
Fixation material	-
Housing Color	White

Optical cover finish	Clear
Overall length	161 mm
Overall width	100 mm
Overall height	211 mm
Dimensions (Height x Width x Depth)	211 x 100 x 161 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.42, 0.39) SDCM<3
Power consumption tolerance	+/-10%

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	ST640T G2 LED39S/PW9 PSU WB WH
Full product name	ST640T G2 LED39S/PW9 PSU WB WH
Full product code	871869691799200
Order code	910500458866
Material Nr. (12NC)	910500458866
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696917992
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696917992

Dimensional drawing



