



# GreenSpace Accent Gridlight

## GD302B LED39S/PW930 PSD-E MB WH

GreenSpace Accent Gridlight, LED module 3500 lm, Premium white with CRI  $\geq 90$ , Power supply unit with DALI interface, DC compatible, external, Beam angle 24°, Safety class II, White

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED lighting and enjoy significant energy savings for a reasonable initial investment. The GreenSpace Accent Gridlight has regular cut-out and specific lumen packages to make retrofit installation quick and easy.

Furthermore, the gridlight products offer multiple system integration and dimming options, including wired as well as wireless. For fashion and food retailers, every GreenSpace Accent Gridlight is available with special LED flavors and fresh food LED lighting recipes to show the merchandise in the very best light. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

### Warnings and Safety

- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

### Product data

General Information		Driver included	Yes
Lamp family code	LED35 [LED module 3500 lm]	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example
Cap-Base	- [-]		
Light source replaceable	No		
Number of gear units	2 units		
Gear	-		

## GreenSpace Accent Gridlight

	B10. Therefore, the median useful life (B50) value also represents the B10 value.
Product family code	GD302B [GreenSpace Accent Gridlight]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	7,800 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	101.2987012987013 lm/W
Color rendering index (CRI)	≥90
Number of light sources	2
Beam angle of light source	120 degree(s)
Light source color	Premium white with CRI ≥90
Optic type	Beam angle 24°
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	24°

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	77 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Polyamide
Housing Color	White
Optical cover finish	Frosted
Overall length	366 mm
Overall width	194 mm
Overall height	100 mm
Dimensions (Height x Width x Depth)	100 x 194 x 366 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.42,0.39) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	GD302B LED39S/PW930 PSD-E MB WH
Full product name	GD302B LED39S/PW930 PSD-E MB WH
Full product code	871869697633300
Order code	910500459125
Material Nr. (12NC)	910500459125
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696976333
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696976333

## GreenSpace Accent Gridlight

### Dimensional drawing

