



# GreenSpace Accent Projector Gen1

## ST320T LED39S/830 PSU VWB BK

GREENSPACE ACCENT PROJECTOR, LED module 3900 lm, 830 warm white, Power supply unit (On/Off), Very wide beam, Black

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Projector's regular 3C adaptor and specific lumen packages make retrofit installation quick and easy. For fashion and food retailers, GreenSpace Accent Projector is available with special light flavors and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

### Product data

General Information			
Lamp family code	LED39 [LED module 3900 lm]	B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Cap-Base	- [-]	Service tag	Yes
Light source replaceable	No	Product family code	ST320T [GREENSPACE ACCENT PROJECTOR]
Number of gear units	1 unit	Lighting Technology	LED
Driver included	Yes	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes

# GreenSpace Accent Projector Gen1

<b>Light Technical</b>	
Luminous Flux	3,900 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	123.80952380952381 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Very wide beam
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	54°
Unified glare rating CEN	Not applicable
<b>Operating and Electrical</b>	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.260 ms
Power Consumption	31.5 W
Power Factor (Fraction)	0.9
Connection	-
Cable	-
Number of products on MCB of 16 A type B	20
<b>Temperature</b>	
Ambient temperature range	+10 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate
Fixation material	Polyamide

Housing Color	Black
Optical cover finish	Clear
Overall length	182 mm
Overall width	114 mm
Overall height	193 mm
Dimensions (Height x Width x Depth)	193 x 114 x 182 mm
<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM<3
Power consumption tolerance	+/-10%
<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes
<b>Product Data</b>	
Order product name	ST320T LED39S/830 PSU VWB BK
Full product name	ST320T LED39S/830 PSU VWB BK
Full product code	871869916671700
Order code	910500459389
Material Nr. (12NC)	910500459389
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699166717
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699166717

# GreenSpace Accent Projector Gen1

## Dimensional drawing

