



LuxSpace Accent Compact Elbow Gen1

RS742B LED27S/FMT PSU-E VWB WH

LuxSpace Accent Compact Elbow Gen1, 35 W, 2700 lm, 3000 K, Very wide beam, White RAL 9003

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today's demanding retail environments. Featuring an extremely compact and unobtrusive form factor, LuxSpace Accent Compact Elbow offers strong optical performance, as well as full aiming options. For fashion and food retailers, it is available with special light flavors and LED recipes to show the clothes and fresh food produce on offer in the very best light.

Product data

General Information			
Lamp family code	LED26S [LED Module, system flux 2600 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	Product family code	RS742B [LuxSpace Accent Compact G3]
Number of gear units	1 unit	Lighting Technology	LED
Driver included	Yes	Value ladder	Specification
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark

LuxSpace Accent Compact Elbow Gen1

Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	2,700 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color rendering index (CRI)	≥85
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	Fresh meat
Optic type	Very wide beam
Optical cover type	-
Luminaire light beam spread	54°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	12.6 A
Inrush time	250 ms
Power Consumption	35 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	43

Temperature

Ambient temperature range	+10 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate

Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	Clear
Overall length	179 mm
Overall width	134 mm
Overall height	109 mm
Overall diameter	134 mm
Dimensions (Height x Width x Depth)	109 x 134 x 179 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.406, 0.350) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No

Product Data

Order product name	RS742B LED27S/FMT PSU-E VWB WH
Full product name	RS742B LED27S/FMT PSU-E VWB WH
Full product code	871869916788200
Order code	910500459493
Material Nr. (12NC)	910500459493
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699167882
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699167882

LuxSpace Accent Compact Elbow Gen1

Dimensional drawing

