



LuxSpace Accent Compact Elbow Gen1

RS742B LED39S/PW930 PSU-E WB WH

LuxSpace Accent Compact Elbow Gen1, 38.5 W, 3900 lm, 3000 K, Wide beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer’s eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today’s demanding retail environments. Featuring an extremely compact and unobtrusive form factor, LuxSpace Accent Compact Elbow offers strong optical performance, as well as full aiming options. For fashion and food retailers, it is available with special light flavors and LED recipes to show the clothes and fresh food produce on offer in the very best light.

Product data

General Information		
Lamp family code	LED39S [LED Module, system flux 3900 lm]	
Light source replaceable	No	
Number of gear units	Unit	
Driver included	Yes	
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Product family code	RS742B [LuxSpace Accent Compact G3]	
Lighting Technology	LED	
Value ladder	Specification	
CE mark	Yes	
Warranty period	5 years	
Flammability mark	For mounting on normally flammable surfaces	

LuxSpace Accent Compact Elbow Gen1

ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	3,900 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	101 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	Premium white with CRI ≥90
Optic type	Wide beam
Optical cover type	-
Luminaire light beam spread	32°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	12 A
Inrush time	100 ms
Power Consumption	38.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate

Optical cover/lens material	Polymethyl methacrylate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	179 mm
Overall width	134 mm
Overall height	109 mm
Overall diameter	134 mm
Dimensions (height x width x depth)	109 x 134 x 179 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.42, 0.39) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	No

Product Data

Order product name	RS742B LED39S/PW930 PSU-E WB WH
Full product name	RS742B LED39S/PW930 PSU-E WB WH
Full EOC	871869916792900
Order code	16792900
Material no. (12 NC)	910500459497
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699167929
Numerator – packs per outer box	1
EAN/UPC - Case	8718699167929

LuxSpace Accent Compact Elbow Gen1

Dimensional drawing

