



# GreenSpace Accent Fixed

## RS340B LED39S/840 PSU-E WB WH

GreenSpace Accent Fixed, 31.5 W, 3800 lm, 4000 K, Wide beam, White

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED lighting and enjoy significant energy savings for a reasonable initial investment. This GreenSpace Accent downlight has regular cut-out and specific lumen packages to make retrofit installation quick and easy. Furthermore, the fixed downlights offer multiple system integration and dimming options, including wired as well as wireless. For fashion and food retailers, every GreenSpace Accent downlight is available with special LED flavors and fresh food LED lighting recipes to show the merchandise in the very best light. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

### Warnings and Safety

- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

### Product data

| General Information      |                                                                                                                              |                                                                                                                                                           |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Light source replaceable | No                                                                                                                           | no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. |
| Number of gear units     | 1 unit                                                                                                                       |                                                                                                                                                           |
| Driver included          | Yes                                                                                                                          |                                                                                                                                                           |
| Remarks                  | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is |                                                                                                                                                           |
| Service tag              | Yes                                                                                                                          |                                                                                                                                                           |
| Product family code      | RS340B [GreenSpace Accent Fixed]                                                                                             |                                                                                                                                                           |
| Lighting Technology      | LED                                                                                                                          |                                                                                                                                                           |

# GreenSpace Accent Fixed

|                   |                                             |
|-------------------|---------------------------------------------|
| Value ladder      | Performance                                 |
| CE mark           | Yes                                         |
| Warranty period   | 5 years                                     |
| Flammability mark | For mounting on normally flammable surfaces |
| ENEC mark         | ENEC mark                                   |
| Glow-wire test    | Temperature 650 °C, duration 30 s           |
| EU RoHS compliant | Yes                                         |

## Light Technical

|                                    |                         |
|------------------------------------|-------------------------|
| Luminous Flux                      | 3,800 lm                |
| Correlated Color Temperature (Nom) | 4000 K                  |
| Luminous Efficacy (rated) (Nom)    | 120.63492063492063 lm/W |
| Color rendering index (CRI)        | ≥80                     |
| Beam angle of light source         | 120 degree(s)           |
| Light source color                 | 840 neutral white       |
| Optic type                         | Wide beam               |
| Luminaire light beam spread        | 36°                     |

## Operating and Electrical

|                                          |              |
|------------------------------------------|--------------|
| Input Voltage                            | 220 to 240 V |
| Line Frequency                           | 50 to 60 Hz  |
| Inrush current                           | 18.6 A       |
| Inrush time                              | 0.240 ms     |
| Power Consumption                        | 31.5 W       |
| Power Factor (Fraction)                  | 0.9          |
| Connection                               | -            |
| Cable                                    | -            |
| Number of products on MCB of 16 A type B | 34           |

## Temperature

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | +10 to +25 °C |
|---------------------------|---------------|

## Controls and Dimming

|                               |                                     |
|-------------------------------|-------------------------------------|
| Dimmable                      | No                                  |
| Driver/power unit/transformer | Power supply unit external (On/Off) |
| Constant light output         | No                                  |

## Mechanical and Housing

|                    |                               |
|--------------------|-------------------------------|
| Housing Material   | Aluminum                      |
| Reflector material | Polycarbonate aluminum coated |

|                        |               |
|------------------------|---------------|
| Optic material         | Polycarbonate |
| Optical cover material | Polycarbonate |
| Fixation material      | Steel         |
| Housing Color          | White         |
| Optical cover finish   | Frosted       |
| Overall height         | 112 mm        |
| Overall diameter       | 190 mm        |

## Approval and Application

|                              |                         |
|------------------------------|-------------------------|
| Ingress protection code      | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard]   |
| Protection class IEC         | Safety class II         |

## Initial Performance (IEC Compliant)

|                             |                     |
|-----------------------------|---------------------|
| Luminous flux tolerance     | +/-10%              |
| Initial chromaticity        | (0.38, 0.38) SDCM<3 |
| Power consumption tolerance | +/-10%              |

## Over Time Performance (IEC Compliant)

|                                                         |     |
|---------------------------------------------------------|-----|
| Control gear failure rate at median useful life 50000 h | 5 % |
| Lumen maintenance at median useful life* 50000 h        | L80 |

## Application Conditions

|                                    |       |
|------------------------------------|-------|
| Performance ambient temperature Tq | 25 °C |
| Suitable for random switching      | Yes   |

## Product Data

|                                 |                               |
|---------------------------------|-------------------------------|
| Order product name              | RS340B LED39S/840 PSU-E WB WH |
| Full product name               | RS340B LED39S/840 PSU-E WB WH |
| Full product code               | 871869917212100               |
| Order code                      | 910500459738                  |
| Material Nr. (12NC)             | 910500459738                  |
| Numerator - Quantity Per Pack   | 1                             |
| EAN/UPC - Product/Case          | 8718699172121                 |
| Numerator - Packs per outer box | 1                             |
| EAN/UPC - Case                  | 8718699172121                 |

## GreenSpace Accent Fixed

### Dimensional drawing

