



StoreSet

SM505T LED90S/830 PSU MB BK

StoreSet track, 830 warm white, Power supply unit (On/Off), Medium beam, Black

Today's retail destinations are all about creating experiences that attract and retain customers. StoreSet adds atmosphere to your store by introducing contrast and breaking up the traditional continuous lines of light. A variety of beam shapes, combined with excellent light quality, ensures that your merchandise stands out, at the same time as enabling you to create a variety of different ambiances. Each StoreSet panel is lightweight and can be easily connected to power tracks or a Maxos fusion backbone. Installation is straightforward, and if your needs change, you can simply adapt the lighting by repositioning the panels and luminaires along the track or trunk. This makes StoreSet a truly flexible, non-linear tool for creating store ambiances that sell.

Warnings and Safety

- The canopy and optical surfaces must only ever be cleaned with a lint-free cloth and without detergents.

Product data

General Information	
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median

	useful life (B50) value also represents the B10 value.
Product family code	SM505T [StoreSet track]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Luminous Flux	9,000 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	122 lm/W
Colour rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	Medium beam
Luminaire light beam spread	38°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	19 A
Inrush time	0.275 ms
Power Consumption	74 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing material	Plastic
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Polyamide
Housing Colour	Black

Optical cover/lens finish	Clear
Overall length	613 mm
Overall width	184 mm
Overall height	75 mm
Dimensions (height x width x depth)	75 x 184 x 613 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Yes

Product Data

Order product name	SM505T LED90S/830 PSU MB BK
Full product name	SM505T LED90S/830 PSU MB BK
Full EOC	871869917234300
Order code	17234300
Material no. (12 NC)	910500459759
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699172343
Numerator – packs per outer box	1
EAN/UPC - Case	8718699172343

Dimensional drawing

