



StoreSet

SM505S LED66S/830 PSD-VLC MB SI

StoreSet trunking, 830 warm white, Power supply unit with DALI interface, Medium beam, Silver

Today's retail destinations are all about creating experiences that attract and retain customers. StoreSet adds atmosphere to your store by introducing contrast and breaking up the traditional continuous lines of light. A variety of beam shapes, combined with excellent light quality, ensures that your merchandise stands out, at the same time as enabling you to create a variety of different ambiances. Each StoreSet panel is lightweight and can be easily connected to power tracks or a Maxos fusion backbone. Installation is straightforward, and if your needs change, you can simply adapt the lighting by repositioning the panels and luminaires along the track or trunk. This makes StoreSet a truly flexible, non-linear tool for creating store ambiances that sell.

Warnings and Safety

- The canopy and optical surfaces must only ever be cleaned with a lint-free cloth and without detergents.

Product data

General Information			
Light source replaceable	No		useful life (B50) value also represents the B10 value.
Number of gear units	Unit	Product family code	SM505S [StoreSet trunking]
Driver included	Yes	Lighting Technology	LED
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	Value ladder	Specification
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Luminous Flux	6,600 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	132 lm/W
Colour rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	Medium beam
Luminaire light beam spread	38°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.280 ms
Power Consumption	50 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Plastic
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel

Housing Colour	Silver
Optical cover/lens finish	Clear
Overall length	575 mm
Overall width	184 mm
Overall height	89 mm
Dimensions (height x width x depth)	89 x 184 x 575 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	SM505S LED66S/830 PSD-VLC MB SI
Full product name	SM505S LED66S/830 PSD-VLC MB SI
Full EOC	871869917245900
Order code	17245900
Material no. (12 NC)	910500459770
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699172459
Numerator – packs per outer box	1
EAN/UPC – Case	8718699172459

Dimensional drawing

