



# Maxos LED inserts for TTX400

## 4MX400 491 LED55S/840 PSD VWB WH C-2R

Maxos LED Retrofit for TTX400, LED Module, system flux 5500 lm, 840 neutral white, Power supply unit with DALI interface, Very wide beam, Connector with 2 additional wires for light regulation, White

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED inserts for TTX400 a truly future-proof solution.

### Product data

General Information		Remarks
Lamp family code	LED55S [LED Module, system flux 5500 lm]	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	
Light source replaceable	No	
Number of gear units	1 unit	
Gear	-	
Driver included	Yes	

# Maxos LED inserts for TTX400

Service tag	Yes
Product family code	4MX400 [Maxos LED Retrofit for TTX400]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

## Light Technical

Luminous Flux	5,500 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	169 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Very wide beam
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	130°
Unified glare rating CEN	Not applicable

## Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.28 ms
Power Consumption	32.5 W
Power Factor (Fraction)	0.9
Connection	Connector with 2 additional wires for light regulation
Cable	-
Number of products on MCB of 16 A type B	24

## Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

## Mechanical and Housing

Housing Material	Steel
Reflector material	-

Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,474 mm
Overall width	63 mm
Overall height	50 mm
Dimensions (Height x Width x Depth)	50 x 63 x 1474 mm

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

## Product Data

Order product name	4MX400 491 LED55S/840 PSD VWB WH C-2R
Full product name	4MX400 491 LED55S/840 PSD VWB WH C-2R
Full product code	871869688246799
Order code	910500460046
Material Nr. (12NC)	910500460046
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696882467
Numerator - Packs per outer box	3
EAN/UPC - Case	8718696882481

## Maxos LED inserts for TTX400

### Dimensional drawing

