



EcoStyle

ST440S LED27S/CH PSU WB WH

EcoStyle Maxos fusion, Champagne, Power supply unit (On/Off), Wide beam, Safety class II, White

Retailers are looking for an affordable LED accent-lighting solution with a reasonable payback compared to conventional technologies. Now, thanks to EcoStyle, they need look no further. With a LED light source and dedicated reflector system, EcoStyle delivers powerful, good-quality accent lighting, enabling retailers to display their merchandise in the best possible light. For food and fashion retailers, EcoStyle is available with special light recipes to further enhance the store ambience and to show the produce and goods on offer in the very best light: Fresh Food Champagne is the perfect LED solution for displaying fruit, vegetables, cheese, bread and pastries in a warm lighting ambience; Fresh Food Meat creates the best light setting for meat enhancement in a cool natural ambience; CrispWhite is the clear choice for fashion retailers to make colors appear rich and intense while keeping whites bright. The track-mounted EcoStyle is also available in a choice of black or white finish. And the combination of efficient LED technology and an innovative heatsink ensures that this is a reliable, lasting solution.

Product data

General Information			
Light source replaceable	No	B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Number of gear units	1 unit	Service tag	Yes
Driver included	Yes	Product family code	ST440S [EcoStyle Maxos fusion]
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	Lighting Technology	LED
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Luminous Flux	2,600 lm
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	110.63829787234043 lm/W
Color rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source color	Champagne
Optic type	Wide beam
Luminaire light beam spread	36°

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.25 ms
Power Consumption	23.5 W
Power Factor (Fraction)	0.95
Connection	-
Cable	-
Number of products on MCB of 16 A type B	34

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate
Fixation material	Polyamide
Housing Color	White

Optical cover finish	Clear
Overall length	189 mm
Overall width	112 mm
Overall height	193 mm
Dimensions (Height x Width x Depth)	193 x 112 x 189 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.4578, 0.4101) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	No

Product Data

Order product name	ST440S LED27S/CH PSU WB WH
Full product name	ST440S LED27S/CH PSU WB WH
Full product code	871869939941200
Order code	910500465320
Material Nr. (12NC)	910500465320
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699399412
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699399412

Dimensional drawing

