



# Selenium

## SGP340 CPO-TW60W K EBR II OR PC LS-8 48/

Vital, MASTER CosmoWhite CPO-TW, 60 W, Electronic regulating, Safety class II, Open CT-POT, Polycarbonate bowl/cover, LumiStep dimming 8 hours, Universal for diameter 48 to 60 mm

Selenium SGP340 is an efficient, ergonomic road-lighting luminaire. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. Selenium incorporates the renowned T-POT reflector for excellent optical performance. Energy savings are possible by means of dimming with a switch or stand-alone Chronosense system (without pilot cable). Selenium is suitable for side-entry or post-top mounting, with a choice of three tilt angles for optimal installation (0, 5, 15°).


### Product data

General Information		Optical cover type	
Lamp family code	CPO-TW [MASTER CosmoWhite CPO-TW]	Polycarbonate bowl/cover	
Cap-Base	PGZ12 [PGZ12]	Optic type outdoor	
Gear	EBR [Electronic regulating]	Open CT-POT	
Photocell	-		
Product family code	SGP670 [Vital]	Operating and Electrical	
CE mark	Yes	Input Voltage	
ENEC mark	-	220 to 240 V	
Embedded control	LumiStep dimming 8 hours	Power Consumption	
		60 W	
		Mechanical and Housing	
		Housing Color	
		Grey	
		Mounting device	
		Universal for diameter 48 to 60 mm	
		Overall height	
		268 mm	
		Approval and Application	
		Ingress protection code	
		IP66 [Dust penetration-protected, jet-proof]	
Light Technical			
Standard tilt angle posttop	5°		
Standard tilt angle side entry	0°		
Number of light sources	1		

Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class II
Product Data	
Order product name	SGP340 CPO-TW60W K EBR II OR PC LS-8 48/
Full product name	SGP340 CPO-TW60W K EBR II OR PC LS-8 48/
Full product code	872790062623000
Order code	910500967812

Material Nr. (12NC)	910500967812
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900626230
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900626230

Dimensional drawing



Product
SGP340 CPO-TW60W K EBR II OR PC LS-8 48/

