



# TownGuide Performer

## BDP101 LED25/740 DN PCC SI CLO-DDF2 76P

TOWNGUIDE PERF BOWL, LED GreenLine 2500 lm, Distribution narrow, Polycarbonate bowl/cover clear, Post-top for diameter 76 mm

The TownGuide Performer family consists of six recognizable yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic, T and Tzero. All are available with a clear bowl. Except for Tzero, also a frosted bowl can be chosen. With an extensive range of lumen packages and a choice of light colors and operating lifetimes, it is easy to select the version that best suits your project's specific requirements. In addition, TownGuide Performer has a variety of control system options that can make it an integral part of your smart energy-reduction programs – from stand-alone LumiStep and DynaDimmer, SDU switch-dim control, through to seamless remote connectivity with CityTouch lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, the luminaire does not have to be opened at all for installation. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, the energy and maintenance cost savings compared to conventional lighting are significant.

### Product data

General Information		Service tag	Yes
Lamp family code	GRN25 [LED GreenLine 2500 lm]	Product family code	BDP101 [TOWNGUIDE PERF BOWL]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Performance
Driver included	Yes	Embedded control	Constant light output and DynaDimmer fixed presets version 2
Photocell	-	CE mark	Yes
Light source engine type	LED		

## TownGuide Performer

Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	No

### Light Technical

Upward light output ratio	0.4
Luminous Flux	2,016 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	119 lm/W
Color rendering index (CRI)	70
Number of light sources	4
Light source color	840 neutral white
Optical cover type	Polycarbonate bowl/cover clear
Luminaire light beam spread	32° x 29°
Optic type outdoor	Distribution narrow

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	17 W
Average CLO power consumption	17.2 W
End CLO power consumption	17.4 W
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	17.4 W
Power Factor (Fraction)	0.95
Connection	Screw connection block 5-pole
Cable	-
Number of products on MCB of 16 A type B 20	

### Temperature

Ambient temperature range	-40 to +35 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-
Constant light output	Yes

### Mechanical and Housing

Housing Material	Aluminum
------------------	----------

Reflector material	-
Optic material	Acrylate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Silver
Mounting device	Post-top for diameter 76 mm
Optical cover shape	Hemispherical
Optical cover finish	Clear
Overall height	293 mm
Overall diameter	570 mm
Effective projected area	0.095 m²
Parts color	All parts colored

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
-------------------------------	-------

### Application Conditions

Maximum dim level	50%
-------------------	-----

### Product Data

Order product name	BDP101 LED25/740 DN PCC SI CLO-DDF2 76P
Full product name	BDP101 LED25/740 DN PCC SI CLO-DDF2 76P
Full product code	871829190612400
Order code	910500991013
Material Nr. (12NC)	910500991013
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291906124
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291906124

## TownGuide Performer

### Dimensional drawing

